

VariCel® M-Pak

HIGH-EFFICIENCY SUPPORTED PANEL FILTERS



- MERV 14, MERV 13, and MERV 11 efficiencies
- 6"-deep (nominal) filter with the same media area and performance as a 12"-deep (nominal) filter
- "Midi" media pack design
- Space-saving design; reduces freight, storage, and handling costs
- Sturdy high-impact polystyrene cell sides enclose a fixed media pack
- Fully incinerable
- MERV 14 and 11 models available with antimicrobial
- MERV 13 and higher meet LEED® Project Certification efficiency requirements



The VariCel® M-Pak filter has the same media area and half the weight of a standard 12"-deep VariCel® filter.


Introduced over a decade ago, the VariCel M-Pak filter performance is still unmatched today in filters with comparable depth. This unique filter offers the same media area as the traditional VariCel 12"-deep filter in a 6"-deep design. The VariCel M-Pak filter delivers comparable efficiency, pressure drop, and overall performance in a much smaller package.

Construction

The header and cell sides of the VariCel M-Pak filter are constructed of high impact polystyrene. The design, which encloses a fixed media pack, creates a rugged filter that resists damage during shipping, handling, and operation. All components of the VariCel M-Pak filter are fully incinerable.

Dual-Density Media

The VariCel M-Pak media pack is constructed with wet-laid fiberglass that is moisture resistant. The VariCel M-Pak filter can withstand exposure to free moisture in the atmosphere, making it ideal for installation in applications where moisture is an issue. The media is manufactured with two layers of glass fibers, coarser fibers on the air entering side and finer fibers on the air leaving side. The media pack is bonded to the cell sides using urethane sealant.



Our dual-density design allows dirt particles to be collected throughout the entire depth of the media pack, utilizing the full filtering potential of the media and maximizing dust holding. Maximizing dust holding capacity extends the life of the filter and minimizes operating costs.

Thermoplastic separators maintain uniform spacing between pleats to allow optimal air both into and through the filter. The separators also ensure a large effective media area to minimize pressure drop and eliminate the need for aluminum separators. Without aluminum separators, risk of damage to the media pack from turbulent or non-laminar airflow is reduced.

VariCel® M-Pak Filters

Designed to Improve Indoor Air Quality

VariCel M-Pak filters with antimicrobial (MERV 14 and 11 models) are designed specifically to improve Indoor Air Quality (IAQ). Air filters are designed to trap and concentrate particulate air contaminants, including viable fungal and bacterial spores. The presence of antimicrobial in the filter media is intended to preserve the integrity of the media throughout the useful life of the filter. Antimicrobial preservatives are not meant to increase the efficiency of the filter, or to kill microorganisms “on the fly.”

Cost-Saving Design

The smaller footprint of the VariCel M-Pak filter means less space is required for storage. VariCel M-Pak filters weigh approximately 8 pounds, less than half the weight of 12”-deep filters with metal cell sides. That means reduced maintenance costs and time savings, as the VariCel M-Pak filter is easier to handle. Additionally, as a result of its reduced depth, the VariCel M-Pak filter is packed two to a carton, lowering freight costs and reducing the amount of space required for storage. The VariCel M-Pak filter also halves disposal volume and reduces disposal costs. Best of all, there is no performance penalty accompanying these savings. The VariCel M-Pak filter meets or exceeds the performance of the 12”-deep filters it replaces.

Specifications

Maximum Operating Temperature: 176°F/80°C

Media: High-efficiency, dual-density, moisture-resistant microglass

Frame: High impact polystyrene (HIPS)


Separators: Hot-melt glue bead

Media Pack Sealant: Urethane

Gaskets: Available on request


Performance Data

Composite Minimum Efficiency Curve



Tested in accordance with ASHRAE Standard 52.2.

Initial Resistance vs. Filter Face Velocity



Filters are rated at 500 FPM filter face velocity. Recommended final resistance for all VariCel M-Pak filters is 1.5" w.g.

Underwriters Laboratories Classification: All VariCel M-Pak filters are UL Classified. Testing was performed according to UL Standard 900.

VariCel® is a registered trademark of AAF International in the U.S. and other countries.



9920 Corporate Campus Drive, Suite 2200, Louisville, KY 40223-5690
888.223.2003 Fax 888.223.6500 | aafintl.com

AAF Flanders has a policy of continuous product research and improvement and reserves the right to change design and specifications without notice.

©2017 AAF International and its affiliated companies.

ISO Certified Firm

AFP-1-161F 02/17